


MCTC-16-3S-1 Cut Sheet



Southwire flexible control cable, shielded, 3 conductors (includes ground), 16 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MCTC-16-3S-1>

Technical Specifications

| | |
|--------------------------------------|--|
| Brand | Southwire |
| Item | Cable |
| Wire/Cable Type | Control |
| UL Wire/Cable Type | TC, TC-ER, WTTC and MTW |
| Application | General purpose |
| Flexibility | Flexible |
| Voltage Rating | 600V (Types TC, TC-ER, MTW), 1000V (Type WTTC) |
| Conductors | 3 conductors (includes ground) |
| Conductor Size | 16 AWG |
| Conductor Stranding | 26-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | PVC/Nylon |
| Conductor Insulation Color | Black with white numbers and green/yellow ground |

| | |
|---------------------------------------|---|
| Shielding | Shielded |
| Jacket Material | TPE |
| Jacket Color | Gray |
| Nominal Overall Cable Diameter | 0.331in |
| Bulk Length | Cut to length |
| Package Type | 1 to 75ft = Coil, 76 to 350ft = 14 x 7in Reel, 351 to 510ft = 14 x 10in Reel, 511 to 790ft = 16 x 10in Reel, 791 to 1110ft = 18 x 10in Reel, 1111 to 1440ft = 18 x 13in Reel, 1441 to 3100ft = 24 x 17in Wooden Reel, 3101 to 5110ft = 30 x 17in Wooden Reel, 5111 to MAX = Large Wooden Reel |

Agency Approvals

| | |
|-------------------------|---|
| UL Listed File # | E75755 |
| CE | None |
| CSA File # | 90458 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |