

# MD250-11Z Cut Sheet



Schmersal heavy duty limit switch, side rotary lever with plastic roller, (1) N.O./ (1) N.C. contact(s), snap action, 122mm hole spacing, cast iron, (2) M25 x 1.5 cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MD250-11Z>

## Technical Specifications

<b>Brand</b>	Schmersal
<b>Item</b>	Limit switch
<b>Switch Type</b>	Heavy duty
<b>Actuator Type</b>	Side rotary lever with plastic roller
<b>Contact Type</b>	(1) N.O./ (1) N.C.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	103mm
<b>Mounting Hole Spacing</b>	122mm
<b>Material</b>	Cast iron
<b>IP Rating</b>	IP65 IP66 IP67
<b>Operating Temperature</b>	-20 degrees to 60 degrees C
<b>Connection</b>	(2) M25 x 1.5 cable entry

## Agency Approvals

<b>UL Listed File #</b>	E57648
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/MD250-11Z.pdf>  
See store item page for other formats.