

MD4-0124T-1 Cut Sheet

ViewMarq MD4 series industrial LED message display, 1 line x 24 characters, 1.5in and 2in, (2) serial and (1) Ethernet port for configuration and external message control, NEMA 4/12, indoor use only.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MD4-0124T-1>

Technical Specifications

| | |
|--|--|
| Brand | ViewMarq |
| Item | Industrial LED message display |
| Series | MD4 |
| Display Size | 1 line x 24 characters |
| Display Type | Tri-color LED |
| Character Size | 1.5in and 2in |
| Character Color | Red, amber and green |
| Character Type | Embedded string and numeric variables |
| Scrolling | Right, left, up and down |
| Recommended Maximum Viewable Distance | 100ft |
| Communication Port and Connection Type(s) | <ul style="list-style-type: none">• (1) Ethernet 10/100Base-T (RJ45)• (1) RS-232 (RJ12)• (1) RS-485 (3-pin terminal) |

| | |
|-----------------------------------|--|
| Port Protocol(s) | Modbus TCP Server, Modbus RTU Slave, ASCII |
| Port Speed(s) | up to 38.4k baud, 10/100 Mbps |
| Housing Material | Extruded aluminum |
| Housing Rating | NEMA 4/12 |
| Environmental Requirements | Indoor use only |
| Includes | Mounting hardware, cable glands and (1) Ethernet patch cable |
| Programming Software | MD-PGMSW configuration software v2.0 or later |
| UL Rating | UL 61010 rated |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E139594 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |