

# MD4-0224T-1 Cut Sheet

ViewMarq MD4 series industrial LED message display, 2 line x 24 characters, 1.5in, 2in and 4in, (2) serial and (1) Ethernet port for configuration and external message control, NEMA 4/12, indoor use only.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MD4-0224T-1>



## Technical Specifications

<b>Brand</b>	ViewMarq
<b>Item</b>	Industrial LED message display
<b>Series</b>	MD4
<b>Display Size</b>	2 line x 24 characters
<b>Display Type</b>	Tri-color LED
<b>Character Size</b>	1.5in, 2in and 4in
<b>Character Color</b>	Red, amber and green
<b>Character Type</b>	Embedded string and numeric variables
<b>Scrolling</b>	Right, left, up and down
<b>Recommended Maximum Viewable Distance</b>	200ft
<b>Communication Port and Connection Type(s)</b>	<ul style="list-style-type: none"><li>• (1) Ethernet 10/100Base-T (RJ45)</li><li>• (1) RS-232 (RJ12)</li><li>• (1) RS-485 (3-pin terminal)</li></ul>

<b>Port Protocol(s)</b>	<ul style="list-style-type: none"><li>• Modbus TCP Server</li><li>• Modbus RTU Slave</li><li>• ASCII</li></ul>
<b>Port Speed(s)</b>	<ul style="list-style-type: none"><li>• up to 38.4k baud</li><li>• 10/100 Mbps</li></ul>
<b>Housing Material</b>	Extruded aluminum
<b>Housing Rating</b>	NEMA 4/12
<b>Environmental Requirements</b>	Indoor use only
<b>Includes</b>	Mounting hardware, cable glands and (1) Ethernet patch cable
<b>Programming Software</b>	MD-PGMSW configuration software v2.0 or later
<b>UL Rating</b>	UL 61010 rated

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/MD4-0224T-1.pdf>  
See store item page for other formats.