

MES-102A-R Cut Sheet



Patlite LED signal tower, (1) tier, 25mm diameter, red, permanent light function, 24 VDC, NPN polarity, clear lens, 40mm body length, silver, 360 degree viewing angle, direct mount, IP42.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MES-102A-R>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number Of Tiers	1
Diameter	25mm
Light Color(s)	Red
Light Function	Permanent
Voltage Rating	24 VDC
Polarity	NPN
Lens Type	Clear
Body Length	40mm
Body Color	Silver
Body Material	Aluminum
Tower Viewing Angle	360 degree
Connector Type	Pigtail
Mounting	Direct
IP Rating	IP42

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	C22.2 No.14
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document