

MET.2.2114R Cut Sheet



SapiSelco stainless steel tooth cable tie, 14.17in length, 0.14in width, 39.69lb tensile strength, 3.98in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MET.2.2114R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Stainless steel tooth
Length	14.17in
Width	0.14in
Tensile Strength	39.69lb
Maximum Bundle Diameter	3.98in
Color	Natural
Material	Nylon
UV Resistant	No
Temperature Rating	-76 to +185 deg F
Installation Temperature	-4 deg F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	100

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document