

MET.2.2123R Cut Sheet



SapiSelco stainless steel tooth cable tie, 7.32in length, 0.18in width, 88.18lb tensile strength, 2.01in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MET.2.2123R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Stainless steel tooth
Length	7.32in
Width	0.18in
Tensile Strength	88.18lb
Maximum Bundle Diameter	2.01in
Color	Natural
Material	Nylon
Temperature Rating	-40 to +185 deg F
Quantity per Pack	100

Agency Approvals

UL Listed File #	E160935
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document