

MET.2.2311R Cut Sheet



SapiSelco stainless steel tooth cable tie, 7.87in length, 0.14in width, 61.73lb tensile strength, 2.17in maximum bundle diameter, natural, nylon. Package of 1000.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MET.2.2311R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Stainless steel tooth
Length	7.87in
Width	0.14in
Tensile Strength	61.73lb
Maximum Bundle Diameter	2.17in
Color	Natural
Material	Nylon
Temperature Rating	-40 to +185 deg F
Quantity per Pack	1000

Agency Approvals

UL Listed File #	E160935
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document