

# MET.2.2323R Cut Sheet



SapiSelco stainless steel tooth cable tie, 7.32in length, 0.18in width, 88.18lb tensile strength, 2.01in maximum bundle diameter, natural, nylon. Package of 1000.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MET.2.2323R>

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Stainless steel tooth
<b>Length</b>	7.32in
<b>Width</b>	0.18in
<b>Tensile Strength</b>	88.18lb
<b>Maximum Bundle Diameter</b>	2.01in
<b>Color</b>	Natural
<b>Material</b>	Nylon
<b>Temperature Rating</b>	-40 to +185 deg F
<b>Quantity per Pack</b>	1000

## Agency Approvals

<b>UL Listed File #</b>	E160935
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>