

# MET.3.2102R Cut Sheet



SapiSelco stainless steel tooth cable tie, 3.94in length, 0.1in width, 39.68lb tensile strength, 0.94in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MET.3.2102R>

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Stainless steel tooth
<b>Length</b>	3.94in
<b>Width</b>	0.1in
<b>Tensile Strength</b>	39.68lb
<b>Maximum Bundle Diameter</b>	0.94in
<b>Color</b>	Black
<b>Material</b>	Nylon
<b>Temperature Rating</b>	-40 to +185 deg F
<b>Quantity per Pack</b>	100

## Agency Approvals

<b>UL Listed File #</b>	E160935
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>