

MET.3.2739R Cut Sheet



SapiSelco stainless steel tooth cable tie, 8.66in length, 0.3in width, 116.87lb tensile strength, 2.2in maximum bundle diameter, black, nylon. Package of 500.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MET.3.2739R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Stainless steel tooth
Length	8.66in
Width	0.3in
Tensile Strength	116.87lb
Maximum Bundle Diameter	2.2in
Color	Black
Material	Nylon
UV Resistant	No
Temperature Rating	-76 to +185 deg F
Installation Temperature	-4 deg F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	500

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document