

MET.3.2748R Cut Sheet



SapiSelco stainless steel tooth cable tie, 13.39in length, 0.28in width, 154.32lb tensile strength, 3.54in maximum bundle diameter, black, nylon. Package of 500.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MET.3.2748R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Stainless steel tooth
Length	13.39in
Width	0.28in
Tensile Strength	154.32lb
Maximum Bundle Diameter	3.54in
Color	Black
Material	Nylon
Temperature Rating	-40 to +185 deg F
Quantity per Pack	500

Agency Approvals

UL Listed File #	E160935
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document