

# MHS06I Cut Sheet



MK Morse hole saw set, 19 pieces, bi-metal cobalt, hardened steel backer, varied tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHS06I>

## Technical Specifications

<b>Brand</b>	MK Morse
<b>Item</b>	Hole saw set
<b>Number of Pieces</b>	19
<b>Material</b>	Bi-metal cobalt
<b>Hole Saw Size</b>	3/4in (19mm), 7/8in (22mm), 1-1/8in (29mm), 1-3/8in (35mm), 1-1/2in (38mm), 1-3/4in (44mm), 2in (51mm), 2-1/4in (57mm), 2-1/2in (64mm), 3in (76mm), 3-1/4in (83mm), 3-5/8in (92mm), 3-3/4in (95mm), 4-1/4in (108mm) and 4-1/2in (114mm)
<b>Cutting Direction</b>	Right hand
<b>Hardened Steel Backer</b>	Yes

<b>Tooth Density</b>	4/6 teeth/in
<b>Toothing</b>	Varied tooth
<b>Set Includes</b>	Includes (15) bi-metal hole saws (3/4in, 7/8in, 1-1/8in, 1-3/8in, 1-1/2in, 1-3/4in, 2in, 2-1/4in, 2-1/2in, 3in, 3-1/4in, 3-5/8in, 3-3/4in, 4-1/4in, and 4-1/2in), (1) 1/4in hex standard arbor assembly, (1) 3/8in hex standard arbor assembly, (1) 7/16in hex pinned arbor assembly, (1) 12in extension, (1) tool storage case
<b>Application</b>	Hole cutting
<b>For Use On</b>	Steel, stainless steel, aluminum, wood, plastic and composite

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>