

MHS08I Cut Sheet



MK Morse hole saw set, 15 pieces, bi-metal cobalt, hardened steel backer, varied tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHS08I>

Technical Specifications

Brand	MK Morse
Item	Hole saw set
Number of Pieces	15
Material	Bi-metal cobalt
Hole Saw Size	3/4in (19mm), 7/8in (22mm), 1in (25mm), 1-1/4in (32mm), 1-3/8in (35mm), 1-1/2in (38mm), 1-3/4in (44mm), 2in (51mm), 2-1/4in (57mm), 2-1/2in (64mm) and 3in (76mm)
Cutting Direction	Right hand
Hardened Steel Backer	Yes
Tooth Density	4/6 teeth/in

Toothings	Varied tooth
Set Includes	Includes (11) bi-metal hole saws (3/4in, 7/8in, 1in, 1-1/4in, 1-3/8in, 1-1/2in, 1-3/4in, 2in, 2-1/4in, 2-1/2in, and 3in), (1) 1/4in hex standard arbor assembly, (1) 3/8in hex standard arbor assembly, (1) 7/16in hex pinned arbor assembly, (1) 12in extension, (1) tool storage case
Application	Hole cutting
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement