

# MHS100 Cut Sheet



MK Morse hole saw set, 11 pieces, bi-metal cobalt, hardened steel backer, varied tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHS100>

## Technical Specifications

Brand	MK Morse
Item	Hole saw set
Number of Pieces	11
Material	Bi-metal cobalt
Hole Saw Size	3/4in (19mm), 7/8in (22mm), 1-1/8in (29mm), 1-3/8in (35mm), 1-1/2in (38mm), 1-3/4in (44mm), 2in (51mm), 2-1/4in (57mm) and 2-1/2in (64mm)
Cutting Direction	Right hand
Hardened Steel Backer	Yes

Tooth Density	4/6 teeth/in
Tooththing	Varied tooth
Set Includes	Includes (9) bi-metal hole saws (3/4in, 7/8in, 1-1/8in, 1-3/8in, 1-1/2in, 1-3/4in, 2in, 2-1/4in and 2-1/2in), (1) 3/8in hex standard arbor assembly, (1) 3/8in hex pinned arbor assembly, (1) tool storage case
Application	Hole cutting
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>