

# MHS14 Cut Sheet



MK Morse hole saw, 7/8in (22mm), bi-metal cobalt, hardened steel backer, varied tooth, 1-15/16in (50mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHS14>

## Technical Specifications

<b>Brand</b>	MK Morse
<b>Item</b>	Hole saw
<b>Hole Saw Size</b>	7/8in (22mm)
<b>Maximum Cutting Depth</b>	1-15/16in (50mm)
<b>Material</b>	Bi-metal cobalt
<b>Hardened Steel Backer</b>	Yes
<b>Tooth Density</b>	4/6 teeth/in

<b>Toothing</b>	Varied tooth
<b>Cutting Direction</b>	Right hand
<b>For Use On</b>	Steel, stainless steel, aluminum, wood, plastic and composite
<b>Application</b>	Hole cutting
<b>Additional Information</b>	Purchase arbor assembly separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>