

MHS22 Cut Sheet



MK Morse hole saw, 1-3/8in (35mm), bi-metal cobalt, hardened steel backer, varied tooth, 1-15/16in (50mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHS22>

Technical Specifications

Brand	MK Morse
Item	Hole saw
Hole Saw Size	1-3/8in (35mm)
Maximum Cutting Depth	1-15/16in (50mm)
Material	Bi-metal cobalt
Hardened Steel Backer	Yes
Tooth Density	4/6 teeth/in

Toothing	Varied tooth
Cutting Direction	Right hand
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite
Application	Hole cutting
Additional Information	Purchase arbor assembly separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement