

MHS23M Cut Sheet



MK Morse hole saw set, 25 pieces, bi-metal cobalt, hardened steel backer, varied tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHS23M>

Technical Specifications

Brand	MK Morse
Item	Hole saw set
Number of Pieces	25
Material	Bi-metal cobalt
Hole Saw Size	3/4in (19mm), 7/8in (22mm), 1in (25mm), 1-1/8in (29mm), 1-3/8in (35mm), 1-1/2in (38mm), 1-3/4in (44mm), 2in (51mm), 2-1/8in (54mm), 2-1/4in (57mm), 2-1/2in (64mm), 2-5/8in (67mm), 3in (76mm), 3-1/4in (83mm), 3-3/8in (86mm), 3-5/8in (92mm), 4-1/8in (105mm) and 4-1/2in (114mm)
Cutting Direction	Right hand
Hardened Steel Backer	Yes

Tooth Density	4/6 teeth/in
Toothing	Varied tooth
Set Includes	Includes (18) bi-metal hole saws (3/4in, 7/8in, 1in, 1-1/8in, 1-3/8in, 1-1/2in, 1-3/4in, 2in, 2-1/8in, 2-1/4in, 2-1/2in, 2-5/8in, 3in, 3-1/4in, 3-3/8in, 3-5/8in, 4-1/8in, 4-1/2in), (1) 3/8in hex standard arbor assembly, (1) 7/16in hex pinned arbor assembly, (2) 1/4in pilot drills, (1) 12in extension, (1) tool storage case
Application	Hole cutting
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement