

# MHS58 Cut Sheet



MK Morse hole saw, 3-5/8in (92mm), bi-metal cobalt, hardened steel backer, varied tooth, 1-15/16in (50mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHS58>

## Technical Specifications

Brand	MK Morse
Item	Hole saw
Hole Saw Size	3-5/8in (92mm)
Maximum Cutting Depth	1-15/16in (50mm)
Material	Bi-metal cobalt
Hardened Steel Backer	Yes
Tooth Density	4/6 teeth/in

Toothing	Varied tooth
Cutting Direction	Right hand
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite
Application	Hole cutting
Additional Information	Purchase arbor assembly separately

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>