

# MI603-AC Cut Sheet



ReeR Micron light grid, sender/receiver pair, measuring, 30mm resolution, 570mm detection height, 0-10m operating distance, (2) push-pull, (2) 4-20mA analog output, configurable, (1) 5-pin M12 quick-disconnect and (1) 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MI603-AC>

## Technical Specifications

<b>Brand</b>	ReeR
<b>Series</b>	Micron
<b>Item</b>	Light grid
<b>Light Curtain Type</b>	Sender/receiver pair
<b>Function</b>	Measuring
<b>Beam Resolution</b>	30mm
<b>Detection Height</b>	570mm
<b>Operating Distance</b>	0-10m
<b>Switching Output</b>	(2) push-pull

<b>Analog Output</b>	(2) 4-20 mA
<b>Configurable</b>	Yes
<b>IP Rating</b>	IP65 IP67
<b>Connection</b>	(1) 5-pin M12 quick-disconnect and (1) 8-pin M12 quick-disconnect
<b>IO-Link Compatible</b>	No
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E469760
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/MI603-AC.pdf>  
See store item page for other formats.