

# MIF03 Cut Sheet



Roxburgh EMI input filter, 120/240 VAC, 1-phase, 3A, panel mount, EMI/RFI filtering, multi-stage, drive rated, very high performance, spring clamp terminals. For use with 1-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MIF03>

## Technical Specifications

|                          |                        |
|--------------------------|------------------------|
| Brand                    | Roxburgh               |
| Item                     | Input filter           |
| Filter Type              | EMI                    |
| Filter Voltage Rating    | 120/240 VAC            |
| Number of Input Phases   | 1                      |
| Amperage Rating          | 3A                     |
| On/Off Switch            | No                     |
| Fused                    | No                     |
| Mounting                 | Panel                  |
| Filtering                | EMI/RFI                |
| Number of Filter Stages  | Multi                  |
| SCCR Rating              | 5kA SCCR               |
| Filter Application       | Drive rated            |
| Filter Performance Level | Very high performance  |
| Connector Type           | Spring clamp terminals |
| For Use With             | 1-phase AC drives      |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | E191581                                |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |