

MIF3150 Cut Sheet



Roxburgh EMI input filter, 230/460 VAC, 3-phase, 150A, panel mount, EMI/RFI filtering, multi-stage, drive rated, very high performance, studs. For use with 3-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MIF3150>

Technical Specifications

Brand	Roxburgh
Item	Input filter
Filter Type	EMI
Filter Voltage Rating	230/460 VAC
Number of Input Phases	3
Amperage Rating	150A
On/Off Switch	No
Fused	No
Mounting	Panel
Filtering	EMI/RFI
Number of Filter Stages	Multi
SCCR Rating	10kA SCCR
Filter Application	Drive rated
Filter Performance Level	Very high performance
Connector Type	Studs
For Use With	3-phase AC drives
Includes	SLV40 protective boots

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191581
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document