

# MIF3180 Cut Sheet



Roxburgh EMI input filter, 230/460 VAC, 3-phase, 180A, panel mount, EMI/RFI filtering, multi-stage, drive rated, very high performance, studs. For use with 3-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MIF3180>

## Technical Specifications

<b>Brand</b>	Roxburgh	<b>Mounting</b>	Panel
<b>Item</b>	Input filter	<b>Filtering</b>	EMI/RFI
<b>Filter Type</b>	EMI	<b>Number of Filter Stages</b>	Multi
<b>Filter Voltage Rating</b>	230/460 VAC	<b>SCCR Rating</b>	10kA SCCR
<b>Number of Input Phases</b>	3	<b>Filter Application</b>	Drive rated
<b>Amperage Rating</b>	180A	<b>Filter Performance Level</b>	Very high performance
<b>On/Off Switch</b>	No	<b>Connector Type</b>	Studs
<b>Fused</b>	No	<b>For Use With</b>	3-phase AC drives

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E191581
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>