

MK7850N-82-200-61 Cut Sheet



Dold multi-mode relay timer, 0.02 seconds to 300 hours selectable timing range, 12-240 VAC/VDC operating voltage, 3A contact rating, (1) SPDT timed relay and (1) SPDT instant or timed configured relay output(s), 35mm DIN rail mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MK7850N-82-200-61>

Technical Specifications

Brand	Dold
Item	Relay timer
Timer Type	Multi-mode
Indicator	LED
Timing Range	0.02 seconds to 300 hours selectable
Operating Voltage	12-240 VAC/VDC
Timer Output Type(s)	(1) SPDT timed relay and (1) SPDT instant or timed configured relay
Timer Function(s)	<ul style="list-style-type: none">• delay on energization• delay on de-energization• delay on energization and de-energization• fleeting• delayed pulse• flasher start with pulse• pulse forming function• fleeting on break

Contact Rating	3A
Mounting	35mm DIN rail
Connector Type	Screw terminal(s)

Agency Approvals

UL Listed File #	E107778
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MK7850N-82-200-61.pdf>
See store item page for other formats.