

MK7873N-82-61-300S Cut Sheet



Dold off-delay relay timer, 15 to 300 seconds timing range, 24-240 VAC/VDC operating voltage, 3A contact rating, (1) DPDT timed relay output(s), 35mm DIN rail mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MK7873N-82-61-300S>

Technical Specifications

Brand	Dold
Item	Relay timer
Timer Type	Off-delay
Indicator	LED
Timing Range	15 to 300 seconds
Operating Voltage	24-240 VAC/VDC
Timer Output Type(s)	(1) DPDT timed relay
Timer Function(s)	off-delay
Contact Rating	3A
Mounting	35mm DIN rail
Connector Type	Screw terminal(s)

Agency Approvals

UL Listed File #	E107778
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document