

MK7873N-82-61-3S Cut Sheet



Dold off-delay relay timer, 0.15 to 3 seconds timing range, 24-240 VAC/VDC operating voltage, 3A contact rating, (1) DPDT timed relay output(s), 35mm DIN rail mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MK7873N-82-61-3S>

Technical Specifications

| | |
|----------------------|----------------------|
| Brand | Dold |
| Item | Relay timer |
| Timer Type | Off-delay |
| Indicator | LED |
| Timing Range | 0.15 to 3 seconds |
| Operating Voltage | 24-240 VAC/VDC |
| Timer Output Type(s) | (1) DPDT timed relay |
| Timer Function(s) | off-delay |
| Contact Rating | 3A |
| Mounting | 35mm DIN rail |
| Connector Type | Screw terminal(s) |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E107778 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MK7873N-82-61-3S.pdf>
See store item page for other formats.