

ML1-025-E-H03R Cut Sheet



Merz rotary disconnect switch, load break capable, 3-pole, 600 VAC, 25A, 5kA SCCR, door mount, UL 508 rated, front operated. Hardware for 4-hole door mounting & lockable red/yellow handle for use with NEMA 4/4X enclosures included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ML1-025-E-H03R>

Technical Specifications

Brand	Merz
Item	Disconnect switch
Fusible	No
Load Break Capable	Yes
Number of Poles	3
Voltage Rating	600 VAC
Amperage Rating	25A
SCCR Rating	5kA SCCR
Mounting	Door
UL Rating	UL 508 rated
Configuration	Front operated
Handle Type	Rotary
Includes	Hardware for 4-hole door mounting & lockable red/yellow handle for use with NEMA 4/4X enclosures
Additional Information	Line and load terminal shrouds sold separately. Suitable as motor disconnect

Agency Approvals

UL Listed File #	E195426
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document