

# ML1-032-E-H03R Cut Sheet



Merz rotary disconnect switch, load break capable, 3-pole, 600 VAC, 32A, 5kA SCCR, door mount, UL 508 rated, front operated. Hardware for 4-hole door mounting & lockable red/yellow handle for use with NEMA 4/4X enclosures included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ML1-032-E-H03R>

## Technical Specifications

<b>Brand</b>	Merz
<b>Item</b>	Disconnect switch
<b>Fusible</b>	No
<b>Load Break Capable</b>	Yes
<b>Number of Poles</b>	3
<b>Voltage Rating</b>	600 VAC
<b>Amperage Rating</b>	32A
<b>SCCR Rating</b>	5kA SCCR

<b>Mounting</b>	Door
<b>UL Rating</b>	UL 508 rated
<b>Configuration</b>	Front operated
<b>Handle Type</b>	Rotary
<b>Includes</b>	Hardware for 4-hole door mounting & lockable red/yellow handle for use with NEMA 4/4X enclosures
<b>Additional Information</b>	Line and load terminal shrouds sold separately. Suitable as motor disconnect

## Agency Approvals

<b>UL Listed File #</b>	E195426
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ML1-032-E-H03R.pdf>  
See store item page for other formats.