

# ML1-032-V-A01 Cut Sheet



Merz manual motor controller, open, 32A, 600 VAC, 3-pole, 20hp, 35mm DIN rail or panel mount, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ML1-032-V-A01>

## Technical Specifications

Brand	Merz
Item	Manual motor controller
Body Type	Open
Amperage Rating	32A
Voltage Rating	600 VAC
Number of Poles	3
Horsepower Rating	20hp
Mounting	35mm DIN rail or panel
Handle Type	Rotary
UL Rating	UL 508 rated
Additional Information	Purchase handle separately. Line and load terminal shrouds sold separately

## Agency Approvals

UL Listed File #	E195426
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ML1-032-V-A01.pdf>  
See store item page for other formats.