

# ML1-032-V-A01 Cut Sheet



Merz manual motor controller, open, 32A, 600 VAC, 3-pole, 20hp, 35mm DIN rail or panel mount, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ML1-032-V-A01>

## Technical Specifications

<b>Brand</b>	Merz
<b>Item</b>	Manual motor controller
<b>Body Type</b>	Open
<b>Amperage Rating</b>	32A
<b>Voltage Rating</b>	600 VAC
<b>Number of Poles</b>	3
<b>Horsepower Rating</b>	20hp
<b>Mounting</b>	35mm DIN rail or panel
<b>Handle Type</b>	Rotary
<b>UL Rating</b>	UL 508 rated
<b>Additional Information</b>	Purchase handle separately. Line and load terminal shrouds sold separately

## Agency Approvals

<b>UL Listed File #</b>	E195426
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>