

ML1-040-V-E02R Cut Sheet



Merz rotary enclosed disconnect switch, load break capable, 3-pole, 600 VAC, 40A, 5kA SCCR, wall mount, UL 508 rated, 7.8 x 7.8 x 6.4in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ML1-040-V-E02R>

Technical Specifications

Brand	Merz
Item	Enclosed disconnect switch
Fusible	No
Load Break Capable	Yes
Number of Poles	3
Voltage Rating	600 VAC
Amperage Rating	40A
SCCR Rating	5kA SCCR
Mounting	Wall
UL Rating	UL 508 rated
Handle Type	Rotary
Housing Size	7.8 x 7.8 x 6.4in
Additional Information	Lockout/tagout capable. Suitable as motor disconnect

Agency Approvals

UL Listed File #	E195426
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document