

# ML2-080-V-E03R Cut Sheet



Merz rotary enclosed disconnect switch, load break capable, 3-pole, 600 VAC, 80A, 5kA SCCR, wall mount, UL 508 rated, 7.8 x 7.8 x 6.4in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ML2-080-V-E03R>

## Technical Specifications

|                               |  |
|-------------------------------|--|
| <b>Brand</b>                  | Merz   |
| <b>Item</b>                   | Enclosed disconnect switch                           |
| <b>Fusible</b>                | No   |
| <b>Load Break Capable</b>     | Yes  |
| <b>Number of Poles</b>        | 3  |
| <b>Voltage Rating</b>         | 600 VAC  |
| <b>Amperage Rating</b>        | 80A  |
| <b>SCCR Rating</b>            | 5kA SCCR   |
| <b>Mounting</b>               | Wall   |
| <b>UL Rating</b>              | UL 508 rated   |
| <b>Handle Type</b>            | Rotary   |
| <b>Housing Size</b>           | 7.8 x 7.8 x 6.4in                                    |
| <b>Additional Information</b> | Lockout/tagout capable. Suitable as motor disconnect |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E195426                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |