

ML3-125-V-A02 Cut Sheet



Merz manual motor controller, open, 125A, 600 VAC, 3-pole, 50hp, 35mm DIN rail or panel mount, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ML3-125-V-A02>

Technical Specifications

Brand	Merz
Item	Manual motor controller
Body Type	Open
Amperage Rating	125A
Voltage Rating	600 VAC
Number of Poles	3
Horsepower Rating	50hp
Mounting	35mm DIN rail or panel
Handle Type	Rotary
UL Rating	UL 508 rated
Additional Information	Purchase handle separately. Line and load terminal shrouds sold separately

Agency Approvals

UL Listed File #	E195426
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document