

MMC-H-131117 Cut Sheet



IDEM safety switch set, non-contact coded magnetic, left exit mount, (2) N.C. safety output(s), (1) N.O. monitoring output(s), 316 stainless steel housing, 36 x 26mm, pigtail, 6.5ft/2m cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MMC-H-131117>

Technical Specifications

| | |
|-------------------------------|----------------------------|
| Brand | IDEM |
| Item | Safety switch set |
| Actuator Type | Non-contact coded magnetic |
| Mounting | Left exit |
| Safety Output Type | (2) N.C. |
| Monitoring Output Type | (1) N.O. |
| IP Rating | IP67 IP69K |
| Indicating Type | LED indication |
| Housing Material | 316 stainless steel |
| Housing Size | 36 x 26mm |
| Connection | Pigtail |
| Conductor Size | 24 AWG |
| Cable Length | 6.5ft/2m |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E300466 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MMC-H-131117.pdf>
See store item page for other formats.