

# MMR-H-131008 Cut Sheet



IDEM safety switch set, non-contact magnetic, right exit mount, (2) N.C. safety output(s), (1) N.O. monitoring output(s), 316 stainless steel housing, 36 x 26mm, 8-pin M12 quick-disconnect, 9.8in/250mm cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MMR-H-131008>

## Technical Specifications

<b>Brand</b>	IDEM
<b>Item</b>	Safety switch set
<b>Actuator Type</b>	Non-contact magnetic
<b>Mounting</b>	Right exit
<b>Safety Output Type</b>	(2) N.C.
<b>Monitoring Output Type</b>	(1) N.O.
<b>IP Rating</b>	IP67 IP69K
<b>Housing Material</b>	316 stainless steel
<b>Housing Size</b>	36 x 26mm
<b>Connection</b>	8-pin M12 quick-disconnect
<b>Cable Length</b>	9.8in/250mm
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E300466
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/MMR-H-131008.pdf>  
See store item page for other formats.