

MOSAIC-MR4 Cut Sheet



ReeR MOSAIC safety relay extension module, 24 VDC, (4) N.O. safety output(s), (2) N.C. monitoring output(s), pluggable screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MOSAIC-MR4>

Technical Specifications

Brand	ReeR
Item	Safety relay extension module
Series	MOSAIC
Control Voltage	24 VDC
Safety Output Type	(4) N.O.
Monitoring Output Type	(2) N.C.
Connection	Pluggable screw terminals

Agency Approvals

UL Listed File #	E343620
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MOSAIC-MR4.pdf>
See store item page for other formats.