

MP-B Cut Sheet



Patlite buzzer element, 80 dB at 1m, 3 kHz tone frequency, continuous tone(s), 24 VAC/VDC, ABS plastic housing, silver, IP65. For use with MP and MPS series signal towers.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MP-B>

Technical Specifications

Brand	Patlite
Item	Buzzer element
Loudness Decibel	80 dB at 1m
Tone Frequency	3 kHz
Tone Type	Continuous
Touch to Acknowledge	No
Voltage Rating	24 VAC/VDC
Housing Material	ABS plastic
Color	Silver
IP Rating	IP65
For Use With	MP and MPS series signal towers

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document