

# MP61 Cut Sheet



Southwire multi-purpose crimping pliers, multiple profile, 22-10 AWG capacity, compatible with insulated and non-insulated terminals and connectors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MP61>

---

## Technical Specifications

<b>Brand</b>	Southwire
<b>Item</b>	Multi-purpose crimping pliers
<b>Crimp Profile</b>	Multiple
<b>Crimp Length</b>	3.0mm/0.12in
<b>Capacity</b>	22-10 AWG
<b>Compatible Connector</b>	Insulated and non-insulated terminals and connectors
<b>Cutting</b>	Beveled cutting edges
<b>Handle Type</b>	Comfort grip handles
<b>Overall Length</b>	9in
<b>Material</b>	Heat-treated steel

---

## Agency Approvals

<b>UL Listed File #</b>	none
<b>UL Recognized File #</b>	none
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	none
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>