

MPB4-5 Cut Sheet



Klemsan MPB4 series splicing connector, lever, side-entry, 5 openings, copper conductor, 18–10 AWG solid, 18–12 AWG stranded, 20A, 600V, polycarbonate housing, transparent/orange. Package of 30.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPB4-5>

Technical Specifications

Brand	Klemsan	Solid Conductor Size	18–10 AWG
Series	MPB4	Stranded Conductor Size	18–12 AWG
Item	Connector	Amperage Rating	20A
Connector Type	Splicing	Voltage Rating	600V
Splice Type	Lever	Housing Material	Polycarbonate
Wiring Direction	Side-entry	Housing Color	Transparent/orange
Number Of Openings	5	Quantity per Pack	30
Conductor Material (PF)	Copper		

Agency Approvals

UL Listed File #	E547252
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document