

MPS-102C-R Cut Sheet



Patlite LED signal tower, (1) tier, 30mm diameter, red, permanent light function, 24 VDC, NPN/PNP polarity, colored lens, 68mm body length, silver, 360 degree viewing angle, direct mount, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPS-102C-R>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number Of Tiers	1
Diameter	30mm
Light Color(s)	Red
Light Function	Permanent
Voltage Rating	24 VDC
Polarity	NPN/PNP

Lens Type	Colored
Body Length	68mm
Body Color	Silver
Body Material	ABS plastic
Tower Viewing Angle	360 degree
Connector Type	4-pin M12 quick-disconnect
Mounting	Direct
IP Rating	IP65

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MPS-102C-R.pdf>
See store item page for other formats.