

MPS-402-RYGB Cut Sheet



Patlite LED signal tower, (4) tiers, 30mm diameter, red/amber/green/blue, permanent light function, 24 VAC/VDC, NPN/PNP polarity, colored lens, 45mm body length, silver, 360 degree viewing angle, direct mount, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPS-402-RYGB>

Technical Specifications

| | |
|------------------------|----------------------|
| Brand | Patlite |
| Item | Signal tower |
| Bulb Type | LED |
| Number Of Tiers | 4 |
| Diameter | 30mm |
| Light Color(s) | Red/amber/green/blue |
| Light Function | Permanent |
| Voltage Rating | 24 VAC/VDC |
| Polarity | NPN/PNP |

| | |
|----------------------------|-------------|
| Lens Type | Colored |
| Body Length | 45mm |
| Body Color | Silver |
| Body Material | ABS plastic |
| Tower Viewing Angle | 360 degree |
| Connector Type | Pigtail |
| Mounting | Direct |
| IP Rating | IP65 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E215660 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | C22.2 No.14 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MPS-402-RYGB.pdf>
See store item page for other formats.