

MPS25-1C-D60A Cut Sheet



ProSense mechanical pressure switch, 8 to 60 psig set point, 316 stainless steel welded diaphragm sensing element, SPDT 3A, 1/4in male NPT process connection, 1/2in male NPT conduit connection with 6ft cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPS25-1C-D60A>

Technical Specifications

| | |
|--------------------------|--|
| Brand | ProSense |
| Item | Mechanical pressure switch |
| Setpoint Range | 8 to 60 psig |
| Sensing Element Material | 316 stainless steel welded diaphragm |
| Switching Output | SPDT 3A |
| Process Connection | 1/4in male NPT |
| IP Rating | IP67 |
| NEMA Rating | 6 |
| Electrical Connection | 1/2in male NPT conduit connection with 6ft cable |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E320431 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 258274 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MPS25-1C-D60A.pdf>
See store item page for other formats.