

MPS25-1C-DV15D Cut Sheet



ProSense mechanical pressure switch, -15 to 15 psig set point, 316 stainless steel welded diaphragm sensing element, SPDT 3A, 1/4in male NPT process connection, DIN 175301-803C L-connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPS25-1C-DV15D>

Technical Specifications

Brand	ProSense
Item	Mechanical pressure switch
Setpoint Range	-15 to 15 psig
Sensing Element Material	316 stainless steel welded diaphragm
Switching Output	SPDT 3A
Process Connection	1/4in male NPT
IP Rating	IP67
NEMA Rating	6
Electrical Connection	DIN 175301-803C L-connector

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	258274
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MPS25-1C-DV15D.pdf>
See store item page for other formats.