

MPS25-1C-P200A Cut Sheet



ProSense mechanical pressure switch, 40 to 200 psig set point, 316 stainless steel piston sensing element, Buna-N O-ring seal(s), SPDT 3A, 1/4in male NPT process connection, 1/2in male NPT conduit connection with 6ft cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPS25-1C-P200A>

Technical Specifications

Brand	ProSense
Item	Mechanical pressure switch
Setpoint Range	40 to 200 psig
Sensing Element Material	316 stainless steel piston
Seal Material	Buna-N O-ring
Switching Output	SPDT 3A
Process Connection	1/4in male NPT
IP Rating	IP67
NEMA Rating	6
Electrical Connection	1/2in male NPT conduit connection with 6ft cable

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	258274
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MPS25-1C-P200A.pdf>
See store item page for other formats.