

MPW40-3-U016 Cut Sheet



WEG Electric MPW40 series manual motor protector, rotary, 16A, thermal overload, 10.0-16.0A adjustable, 208A instantaneous trip rating, open, 45mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPW40-3-U016>

Technical Specifications

Brand	WEG Electric	Power Poles	(3) N.O.
Series	MPW40	Trip Class	Trip Class 10
Item	Motor protector	Phase Loss Sensitive	Yes
Starter Type	Manual	Ground Fault Protection	No
Actuator Type	Rotary	SCCR Rating	50kA SCCR
Amperage Rating	16A	UL Rating	UL 508 rated
Voltage Rating	600 VAC	Enclosure Type	Open
Horsepower Rating	10hp	Frame	45mm
Relay Type	Thermal overload	Mounting	35mm DIN rail
Operation Type	Bi-metallic	Connection	Screw terminal
Full Load Amperage Range	10.0-16.0A adjustable	Additional Information	For UL Type E listing, Power terminal LST25 and Short Circuit Alarm contact block TSB must be added. Suitable as a motor disconnect
Instantaneous Trip Rating	208A		
Number of Poles	3		

Agency Approvals

UL Listed File #	E172121
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document