MR3-480/30 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



BLOCK MR3 series load reactor, 230/480 VAC, 3-phase, 30A, 10 hp at 230 VAC and 25 hp at 480 VAC, open frame, output side only. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/MR3-480/30

Technical Specifications

Brand	BLOCK
Item	Load reactor
Series	MR3
Maximum Voltage	690 VAC
Design Voltage Rating	230/480 VAC
Number of Phases	3
Amperage Rating	30A
Horsepower by Voltage	10 hp at 230 VAC and 25 hp at 480 VAC
Enclosure Type	Open frame
Inductance	0.21
Orientation	Output side only
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	E103521
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/MR3-480_30.pdf
See store item page for other formats.