
MR3-480/6 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



BLOCK MR3 series load reactor, 230/480 VAC, 3-phase, 6A, 2 hp at 230 VAC and 4 hp at 480 VAC, open frame, output side only. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/MR3-480/6

Technical Specifications

Brand	BLOCK
Item	Load reactor
Series	MR3
Maximum Voltage	690 VAC
Design Voltage Rating	230/480 VAC
Number of Phases	3
Amperage Rating	6A
Horsepower by Voltage	2 hp at 230 VAC and 4 hp at 480 VAC
Enclosure Type	Open frame
Inductance	1.06
Orientation	Output side only
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	E103521
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/MR3-480_6.pdf
See store item page for other formats.