

MR604HW Cut Sheet



AttaBox MachoBox series enclosure, NEMA 1/3R/4X/6P/12, 6 x 4 x 5in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MR604HW>

Technical Specifications

Brand	AttaBox
Item	Enclosure
Series	MachoBox
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3R/4X/6P/12
IP Rating	IP66
Nominal Enclosure Height	6in
Nominal Enclosure Width	4in
Nominal Enclosure Depth	5in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Raised hinged screw cover
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64358, E362920
UL Recognized File #	E333478
UL Hazardous File #	none
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MR604HW.pdf>
See store item page for other formats.