

# MRA-10BA-180 Cut Sheet



NITRA pneumatic valve manifold, aluminum, black, rectangular, 1000 psi maximum operating pressure, (10) stations, (1) 1/8in female NPT inlet(s), (20) #10-32 female UNF outlet(s), 180-degree orientation, standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRA-10BA-180>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Valve manifold
<b>Working Fluid</b>	Air or inert gas
<b>Material</b>	Aluminum
<b>Color</b>	Black
<b>Shape</b>	Rectangular
<b>Number of Stations</b>	10
<b>Maximum Operating Pressure</b>	1000 psi
<b>Inlet Port</b>	(1) 1/8in female NPT
<b>Outlet Port</b>	(20) #10-32 female UNF
<b>Mounting Hole Spacing</b>	Standard
<b>Hole Orientation</b>	180-degree

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/MRA-10BA-180.pdf>  
See store item page for other formats.