

MRA-2CB-W Cut Sheet



NITRA pneumatic valve manifold, aluminum, rectangular, 1000 psi maximum operating pressure, (2) stations, (2) 1/4in female NPT inlet(s), (2) 1/8in female NPT outlet(s), wide hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRA-2CB-W>

Technical Specifications

| | |
|-----------------------------------|--------------------------|
| Brand | NITRA |
| Item | Pneumatic Valve manifold |
| Material | Aluminum |
| Shape | Rectangular |
| Number of Stations | 2 |
| Maximum Operating Pressure | 1000 psi |
| Inlet Port | (2) 1/4in female NPT |
| Outlet Port | (2) 1/8in female NPT |
| Mounting Hole Spacing | Wide |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |